


# DUPONT™ TYVEK® ISOCLEAN®

## IC180S OPTION 00

### GARMENT TECHNICAL DATA SHEET



This picture is for measurement reference only.

#### Customer Service:

North America 1-800-931-3456

#### SafeSPEC™ Home Page

Seams and closures have less barrier than fabric. Note: for protection from hazardous or infectious liquids, additional barrier tests are required to establish suitability for use. CAUTION: This information is based upon technical data that DuPont believes to be reliable. It is subject to revision as additional knowledge and experience are gained. DuPont makes no guarantee of results and assumes no obligation or liability in connection with this information. It is the user's responsibility to determine the level of toxicity and the proper personal protective equipment needed. The information set forth herein reflects laboratory performance of fabrics, not complete garments, under controlled conditions. It is intended for information use by persons having technical skill for evaluation under the specific end-use conditions, at their own discretion and risk. Anyone intending to use this information should first verify that the garment selected is suitable for the intended use. In many cases, seams and closures may provide less barrier than the fabric. If the fabric becomes torn, abraded, or punctured, end-user should discontinue use of garment to avoid compromising the barrier protection. **SINCE CONDITIONS OF USE ARE OUTSIDE OUR CONTROL, WE MAKE NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING WITHOUT LIMITATION NO WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR USE AND ASSUME NO LIABILITY IN CONNECTION WITH ANY OF THIS INFORMATION.** This information is not intended as a license to operate under or a recommendation to infringe any patent, trademark or technical information of DuPont or others covering any material or its use. Data presented does not comprise a product specification.

**Warning:** Cleanroom apparel should not be used around heat, flames, sparks or in potentially flammable or explosive environments. Cleanroom fabrics should have slip-resistant materials on the outer sole of boots, shoe covers, or other garment surfaces in conditions where slipping could occur.

**Silicone Statement:** In the past, DuPont has found that threads and zippers can be the most significant source of silicone oil contamination in garments. DuPont specifies that thread and zippers used in DuPont™ Tyvek® IsoClean® and ProClean® garments be manufactured without the use of silicone oils. For end uses with concerns about contamination with silicone oils or any other contaminants, the best practice is to audit inbound materials, including garments, for those contaminants.

**Latex Statement:** As of January 1, 2006, DuPont production specifications exclude use of components containing natural rubber latex in the manufacture of DuPont™ Tyvek® IsoClean® and ProClean® garments. Anyone who begins to exhibit allergic response during the use of DuPont products should immediately cease using these products. The incident should also be reported to DuPont at 1.800.441.3637.

Measurements are approximate values intended to assist in proper size selection. Normal variability may result in slight differences in actual garment sizes.

Copyright © 2019 DuPont de Nemours Inc. All rights reserved. The DuPont Oval Logo, DuPont™, and all products denoted with ® or ™ are trademarks or registered trademarks of DuPont or its affiliates. Printed on:

#### PRODUCT INFORMATION

##### ATTRIBUTES

DuPont™ Tyvek® IsoClean® Coverall. Serged Seams. Attached Elastic Hood. Set Sleeve Design. Elastic Wrists and Ankles. Zipper Closure. White.

##### CATALOG NUMBER

**IC180SWHxx002500 (xx=size)** When ordering, replace xx with desired size.

| FULL PART NUMBER           | FABRIC / MATERIAL        | DESIGN          | SEAM   | COLOR | QUANTITY/BOX | SIZES              | OPTION CODES |
|----------------------------|--------------------------|-----------------|--------|-------|--------------|--------------------|--------------|
| IC180SWHxx002500 (xx=size) | DuPont™ Tyvek® IsoClean® | Hooded Coverall | Serged | White | 25 per case  | MD, LG, XL, 2X, 3X | 00           |

#### TYPICAL FINISHED DIMENSIONS

| SIZE | SLEEVE LENGTH | CHEST WIDTH | INSEAM | FITS CHEST      | FITS HEIGHT | INNER GLOVE SIZE | OUTER GLOVE SIZE |
|------|---------------|-------------|--------|-----------------|-------------|------------------|------------------|
| MD   | 33 3/4        | 24 1/4      | 28     | 35 1/4 - 38 3/4 | 5'3" - 5'7" |                  |                  |
| LG   | 35            | 25 3/4      | 29     | 38 1/4 - 41 3/4 | 5'3" - 5'7" |                  |                  |
| XL   | 36 1/2        | 27 1/4      | 29 1/2 | 41 1/4 - 44 3/4 | 5'5" - 5'9" |                  |                  |
| 2X   | 38 1/4        | 28 3/4      | 30 1/2 | 44 1/4 - 47 3/4 | 5'8" - 6'2" |                  |                  |
| 3X   | 38 1/4        | 30 1/4      | 31 1/2 | 47 1/4 - 50 3/4 | 6'0" - 6'4" |                  |                  |

#### PHYSICAL PROPERTIES - FABRIC DATA

Typical values, not specifications.

| PROPERTY                                     | TEST METHOD | TYPICAL RESULT                    | STD DEV                 |
|----------------------------------------------|-------------|-----------------------------------|-------------------------|
| Basis Weight                                 | ASTM D3776  | 1.22 oz/yd <sup>2</sup>           | 0.04 oz/yd <sup>2</sup> |
| Burst Strength - Mullen                      | ASTM D774   | 54 psi                            | 11 psi                  |
| Breaking Strength - Grab (MD)                | ASTM D5034  | 18 lb <sub>f</sub>                | 2 lb <sub>f</sub>       |
| Breaking Strength - Grab (CD)                | ASTM D5034  | 23 lb <sub>f</sub>                | 3 lb <sub>f</sub>       |
| Hydrostatic Head                             | AATCC 127   | 91 cm H <sub>2</sub> O            | 14 cm H <sub>2</sub> O  |
| Surface Resistivity (25°C / 55% RH)          | ASTM D257   | <6.3 X10 <sup>9</sup> ohms/square |                         |
| Bacterial Filtration Efficiency (3.0 micron) | ASTM F2101  | 99.0 %                            | 0.5 %                   |
| Wearing Apparel Flammability                 | 16 CFR 1610 | Class 1                           |                         |

#### PROCESSING & PACKAGING OPTIONS

Not all options available for all products.

0B or 00 = Bulk; 0C = Clean-Processed; 0S = Sterile; CS = Clean-Processed and Sterile

| OPTION                   | 0B                                                         | 0C                                                                                  | 0S                                                                                  | CS                                                                                  |
|--------------------------|------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| Processing               | -                                                          | Clean-Processed                                                                     | -                                                                                   | Clean-Processed                                                                     |
| Sterilization            | -                                                          | -                                                                                   | Gamma sterilized 10 <sup>-6</sup> Sterility Assurance Level                         | Gamma sterilized 10 <sup>-6</sup> Sterility Assurance Level                         |
| Packaging Conditions     | -                                                          | ISO Class 4 cleanroom                                                               | ISO Class 5 cleanroom                                                               | ISO Class 4 cleanroom                                                               |
| Packaging Configurations | Bulk packaged and placed in double transparent poly liners | Individually packaged in an opaque bag and placed in double transparent poly liners | Individually packaged in an opaque bag and placed in double transparent poly liners | Individually packaged in an opaque bag and placed in double transparent poly liners |